
Pomona®

Model 2451 BNC Female Panel Receptacle



MATERIALS:

Body and Fittings: Brass, Tarnish Resistant Plating Center Contact: Gold Plated Beryllium Copper

Dielectric: PTFE

Finish: Body and Fittings: Tarnish Resistant

Center Contact: Gold Plated

RATING:

Nominal Impedance: 50 Ohms

Operating Temperature: -65°C to +165°C

ORDERING INFORMATION: Model 2451

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02$ " (,51 mm), $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

6/9/99 SY/EH/LS Sales: 909-469-2900 Fax: 909-629-3317 Technical Assistance: 800-241-2060

S:\Engineering\Release\DataSheets\FlukeDataSheet\d2451_1_01.doc

Pomona*ACCESS* **90157** (800) 444-6785 or (949) 253-3858 More drawings available at www.pomonaelectronics.com

Page 1 of 1