

UL CAB UL CAB PC 302018 T



Sample photo

|                      |                                     |
|----------------------|-------------------------------------|
| <b>Order symbol:</b> | UL CAB PC 302018 T                  |
| <b>Product nbr:</b>  | 8143030                             |
| <b>Description:</b>  | UL Cabinet, PC                      |
| <b>Remarks:</b>      | Latches on the long side,<br>smooth |

**EAN:** 6418074053916  
**El. number:**  
 Finland:  
 Electric No. 8212034057  
 Denmark:  
 Electric No. Italy: 7822015U

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

| Dimensions:                  | Length               | Width | Height | Rating:                                  |
|------------------------------|----------------------|-------|--------|------------------------------------------|
| mm:                          | 300                  | 200   | 180    | Ingress Protection (EN 60529): IP65      |
| inch:                        | 11.8                 | 7.9   | 7.1    | Impact Resistance (EN 62262): IK08       |
| Materials:                   |                      |       |        | Electrical insulation: Totally insulated |
| Material:                    | Polycarbonate        |       |        | Halogen free (DIN/VDE 0472, Part 815): 1 |
| Base colour:                 | RAL 7035 -light grey |       |        | UV resistance: UL 508                    |
| Cover colour:                | Smoked grey          |       |        | Flammability Rating: UL 746C 5"          |
| Gasket material:             | EPDM                 |       |        | UL Type:                                 |
| Temperatures:                |                      |       |        | Glow Wire Test (IEC 695-2-1) °C: 960     |
| Temperature °C (short term): | -40 ... 120 °C       |       |        | Certificates:                            |
| Temperature °C (continuous): | -40 ... 80 °C        |       |        | Germanischer Lloyd (GL)                  |
| Temperature °F (short term): | -40 ... 250 °F       |       |        | Underwriters Laboratories                |
| Temperature °F (continuous): | -40 ... 175 °F       |       |        | SGS Fimko                                |
|                              |                      |       |        | Lloyds Register of Shipping (LR)         |
|                              |                      |       |        | UL Canada                                |
|                              |                      |       |        | Gost R                                   |

