



Sample photo

Order symbol: UL PC 125/125 HT
Product nbr: 6411910
Description: UL Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074014627
El. number:
Finland:
Electric No. 8212030213
Denmark:
Electric No. Italy: 7352065U

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm:	130	130	125	
inch:	5.1	5.1	4.9	Ingress Protection (EN 60529): IP66/IP67
Materials:				Impact Resistance (EN 62262): IK08
Material:	Polycarbonate			Electrical insulation: Totally insulated
Base colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws material:	Polyamide			UV resistance: UL 508
Cover colour:	Smoked grey			Flammability Rating: UL 746C 5"
Cover screws colour:	Black			UL Type:
Gasket material:	TPE			Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:				Certificates:
Temperature °C (short term):	-40 ... 120 °C			Germanischer Lloyd (GL)
Temperature °C (continuous):	-40 ... 80 °C			Underwriters Laboratories
Temperature °F (short term):	-40 ... 250 °F			SGS Fimko
Temperature °F (continuous):	-40 ... 175 °F			UL Canada
				Gost R

