



Sample photo

Order symbol: UL PC 125/60 HG
Product nbr: 6411307
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074014320
El. number:
Finland:
Electric No. 8212030268
Denmark:
Electric No. Italy: 7351055U

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm:	130	130	60	Ingress Protection (EN 60529): IP66/IP67
inch:	5.1	5.1	2.4	Impact Resistance (EN 62262): IK08
				Electrical insulation: Totally insulated
				Halogen free (DIN/VDE 0472, Part 815): 1
				UV resistance: UL 508
				Flammability Rating: UL 746C 5"
				UL Type:
				Glow Wire Test (IEC 695-2-1) °C: 960
Materials:				Certificates:
Material:	Polycarbonate			Germanischer Lloyd (GL)
Base colour:	RAL 7035 -light grey			Underwriters Laboratories
Cover screws material:	Polyamide			SGS Fimko
Cover colour:	RAL 7035 -light grey			UL Canada
Cover screws colour:	Grey			Gost R
Gasket material:	TPE			
Temperatures:				
Temperature °C (short term):	-40 ... 120 °C			
Temperature °C (continuous):	-40 ... 80 °C			
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			

