



Sample photo

Order symbol: UL PC B 85 G
Product nbr: 8714304
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074038838
El. number:
Finland:
Electric No. 8212031034
Denmark:
Electric No. Italy: 7201015U

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:			Rating:
Length	Width	Height	Ingress Protection (EN 60529): IP66/IP67
mm:	110	80	Impact Resistance (EN 62262): IK08
inch:	4.3	3.1	Electrical insulation: Totally insulated
Materials:			Halogen free (DIN/VDE 0472, Part 815): 1
Material:	Polycarbonate		UV resistance: UL 508
Base colour:	RAL 7035 -light grey		Flammability Rating: UL 746C 5"
Cover screws material:	Polyamide		UL Type:
Cover colour:	RAL 7035 -light grey		Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:	Grey		Certificates:
Gasket material:	Polyurethane		Germanischer Lloyd (GL)
Temperatures:			Underwriters Laboratories
Temperature °C (short term):	-40 ... 120 °C		SGS Fimko
Temperature °C (continuous):	-40 ... 80 °C		UL Canada
Temperature °F (short term):	-40 ... 250 °F		Gost R
Temperature °F (continuous):	-40 ... 175 °F		

PICCOLO 110x80x65-85

