

UL PICCOLO UL PC MH 125 G



Sample photo

Order symbol: UL PC MH 125 G
Product nbr: 8714319
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074054838
El. number:
Finland:
Electric No. 8212031212
Denmark:

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm:	230	140	125	Ingress Protection (EN 60529): IP66/IP67
inch:	9.1	5.5	4.9	Impact Resistance (EN 62262): IK08
				Electrical insulation: Totally insulated
				Halogen free (DIN/VDE 0472, Part 815): 1
				UV resistance: UL 508
				Flammability Rating: UL 746C 5"
				UL Type:
				Glow Wire Test (IEC 695-2-1) °C: 960
Materials:				Certificates:
Material:	Polycarbonate			Germanischer Lloyd (GL)
Base colour:	RAL 7035 -light grey			Underwriters Laboratories
Cover screws material:	Polyamide			SGS Fimko
Cover colour:	RAL 7035 -light grey			UL Canada
Cover screws colour:	Grey			Gost R
Gasket material:	Polyurethane			
Temperatures:				
Temperature °C (short term):	-40 ... 120 °C			
Temperature °C (continuous):	-40 ... 80 °C			
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			

PICCOLO 230x140x95-125

