

Product availability : Stock - Normally stocked in distribution facility



Main

Range	Multi 9
Product or component type	Undervoltage release
Device short name	MN
[Uc] control circuit voltage	120 V AC 50/60 Hz 24 V DC
Control type	Standard
9 mm pitches	2

Complementary

Range compatibility	Multi 9: Multi 9 C60 C60BP Multi 9: Multi 9 C60 C60BPR Multi 9: Multi 9 C60 C60SP Multi 9: Multi 9 GFP GFP Multi 9: Multi 9 C60H-DC C60H-DC
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	DIN rail
Height	3.25 in (82.5 mm)
Width	0.71 in (18 mm)
Depth	2.68 in (68 mm)
Product weight	0.15 lb(US) (0.066 kg)
Connections - terminals	Clamp terminal bottom 1 cable(s) 0 in ² (2.5 mm ²) rigid (AWG 14) Clamp terminal bottom 2 cable(s) 0 in ² (1.5 mm ²) rigid (AWG 16)
Wire stripping length	0.35 in (9 mm) bottom
Tightening torque	8.85 lbf.in (1 N.m) bottom

Environment

Standards	EN 60947-2 EN/IEC 60947-1
Product certifications	CSA

UL
UR
PCT

Pollution degree	3
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

Ordering and shipping details

Category	00948 - M9 GEN 2 CB UL1077 / IEC
Discount Schedule	DE2
GTIN	00785901761778
Nbr. of units in pkg.	1
Package weight(Lbs)	0.16
Returnability	N