



## Dual-Zone, Dual-Source Stereo Receiver Switching for Four Pair of Speakers



### RX-5502

In our modern, surround sound driven universe, one might think that mere Stereo is old fashioned. But don't be misled. Humans have only two ears and stereo is still a significant life form. Our case in point—the new Sherwood RX-5502. With independent speaker selection for up to 4 pair of loudspeakers, the RX-5502 is adept at powering multi-room audio setups, yet is economical enough to serve a single room. Rated at 70 watts RMS x 4 (with 100 watts per channel into 4 ohms), distortion is less than 0.20% from 20 Hz to 20 kHz into 8 ohms.

#### Key Features

- Totally Discrete Amplifiers for all channels (TDAS)
- Switching for four pair of loudspeakers (in parallel)
- 25-Key Remote Control
- Phono Input
- AM and FM Stereo Tuning
- 30 Station Presets
- 5 Audio Inputs (Including Tuner)
- Sleep Timer
- Bass and Treble Tone Controls

#### General Features

- Digital Encoder Volume Control
- System Illumination (Dimmer)
- Headphone Jack

#### Dimensions and Weight

- 17 3/8" W x 5" H x 13"
- 18 lbs.

#### Performance Ratings

- Input Sensitivity 200 mV
- IM Distortion (rated output) <0.3%
- S/N Ratio 90 dB
- IHF FM Sensitivity 17.2 dBf
- Tuner S/N Ratio (Mono/Stereo) 68 /68 dB
- FM THD (Mono/Stereo) 0.3%/0.4%
- Selectivity 55 dB
- Stereo Separation 40 dB
- FM Frequency Response 40– 12 kHz, +/- 1 dB
- AM Sensitivity 800 uV/M
- AM Frequency Response 100 Hz–2.3 kHz
- Tone Direct
- Large Fluorescent Display
- UPC Code: To be announced



Due to ongoing product improvements, Sherwood reserves the right to change product specifications without prior notification.

All trademarks and registered trademarks are of their respective owners.