



Model #: CPS-1215RM

UPC: 649532893508

MSRP: \$49.99



Title

CPS-1215RM Rackmount PDU Power Strip - 10-Outlet 15A 1800VA

Description

The CyberPower Power Distribution Unit (PDU) provides additional outlets for your rackmount power needs. The 1215RM offers 10 (ten) 15A rear-mounted outlets in the 19 inch 1U case. The rugged metal housing can withstand the most demanding environments and a 15 ft cord ensures compatibility for most rackmount applications. Also note that CyberPower PDUs can be wall mounted, desktop, or under-cabinet mounted for use in retail, security, POS, telecommunications, networking, audio/video displays or anywhere dedicated power distribution is needed.

Features

- EMI/RFI Shielding: Provides shielding against electromagnetic interference & radio frequency signals. Most commonly, this is used to prevent line noise or humming that occurs over telephone lines or stereo electronics.
- Resettable Circuit Breaker: Convenient unit reset in case of an overload.
- ISO & Safety Certifications: All CyberPower manufacturing facilities are ISO-9001 Quality Tested. Our products are also UL Registered.

Technical Specifications

Technical Information	
Input Receptacles	NEMA 5-15P
Output Receptacles (Rear)	10 x NEMA 5-15R
Output Receptacles (Front)	None
Power Description	
Input Voltage	110 V AC to 120 V AC
Output Voltage	120 V AC
Current	15A
Frequency	60 Hz
Load/Power Rating	1800VA
Filtering	EMI/RFI
Circuit Breaker	1 x 15A
Controls/Indicators	
Status Indicators	<ul style="list-style-type: none"> • Power On (Red)
Environmental Conditions	
Temperature	<ul style="list-style-type: none"> • 32 °F (0 °C) to 95 °F (35 °C) Operating • 5 °F (-15 °C) to 113 °F (45 °C) Non-operating
Humidity	<ul style="list-style-type: none"> • 0 to 95% Non-condensing Operating Humidity • 0 to 95% Non-condensing Non-operating
Altitude	<ul style="list-style-type: none"> • 0 ft to 10000 ft Operating • 0 ft to 50000 ft Non-operating
Physical Characteristics	
Color	Black
Form Factor	1U 19" Rack-mountable
Power Cord/Cable	1 x 15ft 15A Power Cord
Dimensions	1.75" Height x 19" Width x 4.25" Depth
Shipping Dimensions	2.25" Height x 20.5" Width x 10" Depth - Display Box
Weight	4.9 lb
Shipping Weight	5.5 lb - Display Box
Miscellaneous	
Package Contents	<ul style="list-style-type: none"> • CPS-1215RM Unit • Warranty Card/Manual
Certifications & Standards	UL Recognized
Country of Origin	China
Warranty	
Standard Warranty	3 Year(s) Parts & Labor
Additional Warranty Information	<ul style="list-style-type: none"> • CyberPower stands behind its products by offering an industry leading 3-year warranty. CyberPower also has a #1 rated technical support team that will assist you with product, installation, or warranty concerns --- Free of charge.