


# CABLE SPECIFICATION

SPEC NO. : RG6/U SIAMESE COAXIAL CABLE

Customer No. 24-10246

Construction Item		Unit	Construction Item
Conductors	Construction	mm	1/1.02±0.05
	Material	---	CU
	Filler Material	---	---
	O. D.	mm	1.02±0.05
Insulators	Material	---	Foamed PE
	Diameter	mm	4.57±0.01
	Average Thickness	mm	1.77±0.05
	Colour	---	White
Outer Conductors	AL-PET Foil	um	AL-P-AL
	Type	---	Braid
	Material	---	ALMG
	Coverage	%	60%
	Diameter	mm	4.80±0.15
Jacket	Material	---	PVC (CM)
	Diameter	mm	6.9±0.15
	Average Thickness	mm	1.0±0.10
	Extrusion	---	---
	Surface	---	---
	Colour	---	Black
Power Wire	Construction	mm	16*0.254CU
	Diameter	mm	3.2PVC
Inking	Inking Colour	---	White
	Inking	---	Stellar Labs SIAMESE RG6/U TYPE COAX 75OHM 18AWG 75degC 2250MHz +2C18 E188601 (UL) CM RoHS COMPLIANT
Line	Length	ft	1000

**CONFIGURATION:**



GENERAL TOLERANCES (UNLESS SPECIFIED)

LENGTH: X ± 1  
           .X ± 0.2  
           .XX ± 0.10  
 ANGLE: X° ± 1°  
           .X° ± 0° 30'



UNIT: mm	REV:	↔ ⊕	NAME	RG6/U SIAMESE COAXIAL CABLE
DRAWING	XIAOSHENG 2008/10/07	S. P. NO.		
CHECK		P. O. NO.	DWG. NO.	
APPROVE		SIZE	PAGE	1/1