




ISS	ZONE	DESCRIPTION\PER REQUEST\DATE
A2	C-5	加包材
V	OPEN	對客戶公開圖紙
	OPEN	對供應商公開圖紙
	CLOSED	僅限廠內使用

Stellar Labs - 110 ohm DMX-512 & AES/EBU Patch Cord

- NOTES:
- HOUSING WITH A FLOWER LOGO (鍍殼上有花型商標)
 - 1PCS 用一個 Stellar Labs 塑袋包裝並封口
封口機溫度須控制在 200 度
 - RoHS 貼紙與品名貼紙, 須注意貼至
塑袋"正面置中"處




CABLE NO.: 4101020238
3070100119-91



Stellar Labs
小號塑膠袋 (200mmX270mm)
中號塑膠袋 (270mmX350mm)
RoHS 貼紙 (20mmX10mm)
品名貼紙 (45mmX18mm)

	LENGTH	ITEM	Stellar Labs袋	貼紙
	3FT (915 ± 30)	555-11900	小	V
	6FT (1835 ± 30)	555-11901	小	V
	10FT (3050 ± 50)	555-11902	小	V
	15FT (4575 ± 80)	555-11903	中	V
	30FT (9150 ± 100)	555-11904	中	V
	50FT (15250 ± 100)	555-11905	中	V
	75FT (22875 ± 100)	555-11906	中	V
	100FT (30500 ± 100)	555-11907	中	V



3	CONNECTOR	Zznl14-1	鍍銀(NICKEL)	1	SVP555S-NL
2	CABLE		黑色(BLACK)	1	3070100119-91
1	CONNECTOR	Zznl14-1	鍍銀(NICKEL)	1	SVP556S-NL
NO.	DESCRIPTION	MATERIAL	FINISH	QTY	DRAWING NO.

DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED		APPROVED	DATE	2011-10-11
TOLERANCES		CHECKED	DATE	2011-10-10
ANGLES = ±5°		DRAWN	DATE	2011-10-09
UP TO 6 = ±0.2		FILE NO.	TITLE	
6-40 = ±0.4		ERP LINK:	SVP555S/556S-NL+3070100119-91	
40-120 = ±0.6		SCALE	(3FT/6FT/10FT/15FT/30FT/50FT/75FT/100FT)	
120-315 = ±1			PART NO.	
ABOVE 315 = ±1.6			REV. A2	