


CUSTOMER	MCM
PRODUCT NO.	24-120** series



SIDE:A

SIDE:B

CUSTOMER P/N	24-12050	24-12051	24-12052	24-12053	24-12054	24-12055
L±T(MM)	460±10	920±10	1830±20	3660±20	7620±40	15240±100
Tie(MM)	60MM	80MM	110MM	130MM	160MM	PE film 600MM
Winding ø(MM)	100±15		120±15		140±15	170±15
MCM Nylon bag	200*270*0.06MM					270*350*0.06MM

**NOTE:**

- (1).Cable Spec: SLV Series AUDIO/VIDEO Interconnect Cable[(10/0.12BC)\*2C(WHITE/RED)+S(32/0.10BC)]  
 Jacket Material:PVC OD:4.0mm  
 Cable Colour: Cool Grey 11C  
 Cable Printing:SLV Series AUDIO/VIDEO Interconnect Cable www.stellarlabs.com


- (2).Connector A: 3.5mm Male Solder Type  
 INSULATION:Black  
 CONTACTS:Nickel Plated
- (3).Connector B: 3.5mm Male Solder Type  
 INSULATION:Black  
 CONTACTS:Nickel Plated

(4).Over Mold: PVC-45P-Cool Grey 11C

(5).Parameter Settings: CT-8681FA


1. Conductive Resistance:1.0Ω
2. Insulative Resistance:5MΩ (Min.)
3. Hi-Pot:300V/AC、DC , 1.5mA/I , 50Hz , 0.03s

- (6).100% OPEN, SHORT&MISWIRE TEST;  
 (7).ALL MATERIALS MUST BE IN LINE WITH RoHS.  
 (8).Packing:Nylon bag+label



- 24-12051 3FT Bar Code:8 82459 00865 9  
 24-12052 6FT Bar Code:8 82459 00866 6  
 24-12053 12FT Bar Code:8 82459 00867 3  
 24-12054 25FT Bar Code:8 82459 00868 0  
 24-12055 50FT Bar Code:8 82459 00869 7

<u>SIDE:A</u>		<u>SIDE:B</u>	
ø3.5 PLUG		ø3.5 PLUG	
1	WHITE	1	
2	RED	2	
3	F	3	



PIN OUT: (5)

PACKING : (8)

0	NEW	2014/04/04
REV	DESCRIPTION	DATE

GENERAL TOLERANCES (UNLESS SPECIFIED)		MCM Electronics				www.mcmelectronics.com	
LENGTH: X. ±1 .X±0.2 .XX±0.10		UNIT:mm	REV:0/A			NAME	AUDIO CABLE
ANGLE: X° . ±1° .X° ±0° 30'		DRAWING	XIAODENG	2014/04/04	S. P. NO.	HT-5762	DC3.5 Stereo M/M
		CHECK			P. O. NO.		DWG. NO.
		APPROVE			SIZE		PAGE
							1/1