





CUSTOMER	MCM	FILE NO.	26-745	THIS DRAWING AND SPECIFICATIONS, HEREIN ARE THE CONFIDENTIAL PROPERTY OF SAMAR AND SHALL NOT BE REPRODUCED OR COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT WRITTEN PERMISSION.	REV.	DESCRIPTION	DRAWN / DATE	APPROVED / DATE
					0	INITIAL RELEASE	YANG 08/25/2011	FR0S 08/25/2011



Panel Thickness: 2.5mm Max.



SPECIFICATION

1. Rating : AC 125V 16A 250V 10A
2. Contact R. : 50m Ω Max.
3. Insulation R. : DC 500V 100M Ω Min.
4. Dielectric Strength : AC 1500V 1 minute
5. Electrical Life : 20,000 make-and-break cycles at full load.

DIMENSIONS ARE IN mm [INCH]	TOLERANCES ARE FRACTIONS DECIMALS ANGLES	MATERIAL	4P ILLUMINATED ROCKET SWITCH, DPST			P/N 26-745	DRAWN YANG	DATE 08/25/2011
MOLD NO.	.X $\pm$ 0.20 [0.008]	FINISH				PROJECT NO.		
26-745	.XX $\pm$ 0.12 [0.005]	COLOR				SCALE 1.25:1	SIZE A4	SHEET 1 OF 1