

a-live[™] Multi-Room Audio System

Play mulitple song files or audio playlists in up to different 6 zones simultaneously from the same PC without appropriating any of a-live's 6 built-in source inputs.



AKPA

Interactive LCD Keypad

A6X6A70 70/25 Volt version

A6X6A8 8 Ohm version

a-live™ allows you to play networked digital music directly from your PC to any and all zones. Streamed audio files can be played from the same playlist simultaneously among different zones. For example, if a user is in zone one, and selects a particular song to start playing, a different user in any of the other zones can select the same exact song to play, from the beginning, without interfering with the current play in zone one. Or they could choose to play a completely different song, and aren't limited by having to share a source unit such as an MP3 player or CD player. Most major unprotected formats are supported.

An intuitive GUI interface allows you to remotely program and control any zone from a PC, and also turns a laptop on the same network with wireless LAN capabilities into a master remote control. Additionally, for large-scale environments, dozens of a-live units can be networked together and all controlled via the same GUI.

Optional a-live™ interactive keypads come with 1" blue backlit LCD screens to provide you total zone control, including volume controls w/ mute, tone controls, and full control of all PC-based music including forward, back, pause and scrolling information of artist and song name. Keypads also have IR remote control capability for external source devices such as CD players, home theater audio, etc.

Features Audio source inputs: 6 Zones per unit: 6 Multiple server management on LAN: Yes Keypad ports: RS-422 Interface ports: RJ-45 for 100Mbps LAN (Ethernet), RS-232 for system diagnostics Source input connectors: RCA jacks (left and right) Source input impedance: 50k ohm Source input level: 2.2 Vrms max Amplifier channels: 6 channels (A6X6A70) / 12 channels (A6X68) Speaker impedance (Nominal, minimum): 8 ohms nominal, 6 ohms minimum (A6X68) Speaker connectors: Removable 4-pole coded snap Audio line outputs: 2.2Vrms (Fixed) Power rating: 100-120VAC 3A or 220-240VAC 1.25A, 50-60Hz Fuse rating: F3.0A H 250V USA and Canada

Specifications subject to change