

3/4" Steel Door Recessed-Mount Contact

SM-4105-LQ/B

1" (25mm) Gap, Closed Loop, Brown, with 18" (46cm) leads

SM-4105-LQ/W

1" (25mm) Gap, Closed Loop, White, with 18" (46cm) leads

Features:

- Used for steel framed doors and windows where space is limited or to avoid unsightly installations
- Strong one-piece construction
- 18" (46cm) wire leads
- High-impact ABS plastic
- Switch and magnet have ribs for securing in holes
- Contact reed switch is SPST, iridium-plated to have a high melting point and Vickers hardness for higher power handling and longer expected life
- · For closed loop circuits
- 1" (25mm) Gap
- · Lifetime limited warranty










18" Wire Leads



Specifications:

Model Number		SM-4105-LQ/B	SM-4105-LQ/W
Circuit type		Closed loop	
Operation gap		1" (25mm)	
Color		Brown	White
Material	Case	High-impact ABS plastic	
	Terminal	18" (46cm) leads	
Contacts		Iridium-plated	
Contact rating		0.1A@100VDC (max)	
		1.0A@10VDC (max)	
		10W (max)	
Temperature		-68° ~ 158° F (-20° ~ 70° C)	
Switch cycles		50 Million (0.1mA@5VDC)	
Switch dimensions		1 ³ / ₁₆ "x ¹⁵ / ₁₆ "x ³ / ₄ " (30x24x19mm)	
Magnet dimensions		1 ³ / ₁₆ "x ¹⁵ / ₁₆ "x ³ / ₄ " (30x24x19mm)	
Magnet		Rare-earth Neodymium Alloy	

Dimensions:



SECO-LARM® U.S.A., Inc.

16842 Millikan Avenue, Irvine, CA 92606 Phone: (949) 261-2999 | (800) 662-0800 Fax: (949) 261-7326 Website: www.seco-larm.com Email: sales@seco-larm.com Copyright 2015 © SECO-LARM U.S.A., Inc. All rights reserved All trademarks are the property of SECO-LARM U.S.A., Inc. or their respective owners. The SECO-LARM policy is one of continual development. For that reason, SECO-LARM reserves the right to change prices and specifications without notice. SECO-LARM is not responsible for misprints