



### Main

Range of product	Mureva BOX
Product or component type	Junction box
Colour tint	Grey RAL 7035
Quantity per set	1 piece

### Complementary

Wiring device mounting	Surface
Cable entry	Grommets
Fixing mode	Screw-fixed cover
Base dimension	150 x 105 x 80 mm
Cable entry number	10 grommets Ø 25 mm
Material	PP (polypropylene) cover SBS (styrene butadiene styrene) grommet
Electrical insulation class	Class II according to IEC 536
Height	85 mm
Width	165 mm
Depth	125 mm

### Environment

Ambient air temperature for operation	-25...40 °C
IP degree of protection	IP55 according to IEC 60529
IK degree of protection	IK07 according to EN 50102
Fire resistance	750 °C
Standards	EN 60670
Product certifications	CE
Environmental characteristic	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1026 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------