

For more Information
please call

1-800-Belden1



General Description:

EPDM high temperature lead wire. 150C EPDM wire is recommended for Class 130(B) , 155(F) and also in some 180(H) systems. It's UL Recognized under Style 3374 as 150C-600V Appliance Wiring Material. The CSA Listing, as a coil lead, is 125C, 600V.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	14	41x30	TC - Tinned Copper

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
EPDM - Ethylene Propylene Diene Monomer Rubber	.045

Overall Insulation

Overall Cable

Overall Nominal Diameter: 0.169 in.

Mechanical Characteristics (Overall)

UL Temperature Rating: 125°C (UL AWM Style 3340), 125°C (UL AWM Style 3374), 150°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL AWM Style: UL Style 3340 (600 V 125°C), UL Style 3374 (600 V 125°C)

UL Rating: 600 V, 150°C

CSA Rating: 600 V, 125°C

CSA Type: CL1254

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MIL Order #39 (China RoHS): Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Max. Operating Voltage - UL:

Voltage
600 V RMS (UL AWM Style 3340)
600 V RMS (UL AWM Style 3374)

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
37114 0024000	4,000 FT	96.000 LB	RED	C I Z	#14STR EPDM 150C 600VRED
37114 002500	500 FT	12.500 LB	RED	F	#14 STR EPDM 150C 600V

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

37114 Hook-up/Lead - UL AWM Style 3340 and 3374

37114 0104000	4,000 FT	96.000 LB	BLACK	C I	#14STR EPDM 150C 600VBLK
37114 010500	500 FT	12.500 LB	BLACK	F	#14 STR EPDM 150C
37114 0105000	5,000 FT	125.000 LB	BLACK	C	#14 STR EPDM BLK

Notes:

C = CRATE REEL PUT-UP.

F = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'

I = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 200'

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 08-02-2012

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.