Product datasheet Characteristics

NSYCAG92LPF

outlet grille plast cut out 92x92mm ext dim 137x117mm IP54



Main

IVIAIII		
Range	ClimaSys	
Range compatibility	ClimaSys CV fan	
Product or component type	Outlet grille	
Accessory / separate part destination	ClimaSys ventilation system	
Fixing mode	By screws Clipped	
Device composition	1 x external part (front) 1 x G2 M1 synthetic standard filter (rear of outlet grille) 1 x support frame	

Complementary

Schypider ==		
Main		
Range	ClimaSys	
Range compatibility	ClimaSys CV fan	
Product or component type	Outlet grille	
Accessory / separate part destination	ClimaSys ventilation system	
Fixing mode	By screws Clipped	
Device composition	1 x external part (front) 1 x G2 M1 synthetic standard filter (rear of outlet grille) 1 x support frame	
Complementary		
Material	Injected thermoplastic (ASA PC)	
Colour	Grey (RAL 7035) external part	
Cut-out dimensions	92 x 92 mm	
Height	External : 137 mm	
Width	External : 117 mm	
Depth	External : 13 mm	
Offer Sustainability		
Sustainable offer status	Not Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
	Reference not containing SVHC above the threshold	
Contractual warranty		
Warranty period	18 months	
May 00, 2047		

Offer Sustainability

Sustainable offer status	Not Green Premium product	7
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity	
	Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
	Reference not containing SVHC above the threshold	

Contractual warranty

Warranty period	18 months	