



Main

Range	ClimaSys
Product name	ClimaSys CC
Product or component type	Simple thermostat
Temperature setting range	0...60 °C
Information displayed	Temperature in °C

Complementary

Input voltage	250 V
Sensor type	Bimetal
Contacts type and composition	NO
Contact resistance	< 10 mOhm
Service life in cycles	>= 100000 cycles
Maximum switching capacity	10 A 250 V AC resistive 15 A 120 V AC resistive 30 W DC 2 A 120...250 V AC inductive pf: 0.6
Electrical connection	4 terminals 2.5 mm ²
Mounting mode	Clipped
Height	External : 68 mm
Width	External : 33 mm
Depth	External : 44 mm
Product weight	40 g
Mounting location	On mounting plate 35 mm DIN rail Spacial upright Cross rails
Ambient air temperature for operation	-20...80 °C
IP degree of protection	IP20
Hysteresis	7 %

Number of outputs	1 output(s) ventilation function
Material	PC
Colour	Light grey
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product certifications	UL

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------