Product datasheet Characteristics

XACA9415

round head for pushbutton - spring return - XAC-A - yellow - booted



Main

		ā
Range of product	Harmony XAC	
Product or component type	Head for push-button	**************************************
Component name	XACA	

Complementary

Marking	Unmarked
Operator additional information	Booted
Cap/Operator or lens colour	Yellow
Product compatibility	XACA
Mounting location	Front of enclosure
Sale per indivisible quantity	10
Standards	EN/IEC 60204-32 UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14
Ambient air temperature for operation	-2570 °C
Ambient air temperature for storage	-4070 °C
Vibration resistance	15 gn 10500 Hz IEC 60068-2-6
Shock resistance	100 gn IEC 60068-2-27
Overvoltage category	Class II IEC 61140
IP degree of protection	IP65 IEC 60529
IK degree of protection	IK08 EN 50102
Product weight	0.01 kg

Contractual warranty

Warranty period	18 months
-----------------	-----------