ZCKD02
limit switch head ZCKD - steel roller plunger

Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Plunger head
Product compatibility	XCKM XCKL XCKS
Associated body	ZCKMD37 ZCKM1H29 ZCKSD35 ZCKS9 ZCKL7H7 ZCKM8 ZCKMD39H29 ZCKM8H7 ZCKL5 ZCKSD31 ZCKL8 ZCKLD31H7 ZCKS8 ZCKS2 ZCKMD31H7 ZCKS1 ZCKS6H29 ZCKMD31 ZCKLD37 ZCKMD37H7 ZCKM7H29 ZCKSD39 ZCKSD37H29 ZCKL1 ZCKS7 ZCKSD37 ZCKM9 ZCKL5H7 ZCKMD35 ZCKL7 ZCKM1

Life Is On | Schneider Electric

ZCKS5
ZCKM1H7
ZCKM9H29
ZCKSD39H29
ZCKSD31H29
ZCKL6
ZCKL8H7
ZCKS2H29
ZCKLD31
ZCKL1H7
ZCKLD35
ZCKM5H29
ZCKSD35H29
ZCKS9H29
ZCKLD37H7
ZCKL6H7
ZCKLD39
ZCKMD31H29
ZCKM7H7
ZCKM6
ZCKM5
ZCKS7H29
ZCKM8H29
ZCKLD39H7
ZCKMD39H7
ZCKS5H29
ZCKM7
ZCKLD35H7
ZCKM6H29
ZCKMD35H7
ZCKS1H29
ZCKS6
ZCKMD35H29
ZCKMD37H29
ZCKS8H29
ZCKMD39
ZCKM5H7
ZCKM6H7

Movement of operating head	Linear
Type of operator	Roller plunger spring return metal
Type of approach	Lateral approach 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Plastic

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0922 - Schneider Electric declaration of conformity 🔗 Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months

Life Is On | Schneider Electric