

Zelio relay range



Main

Range of product	Zelio Relay
Product or component type	Socket
Contact terminal arrangement	Mixed
Product compatibility	Plug-in relay RXM (2 C/O)
Device short name	RXZ
Sale per indivisible quantity	10

Complementary

[I _{th}] conventional free air thermal current	7 A
[U _e] rated operational voltage	250 V
Tightening torque	≤ 0.8 N.m (M3 screw(s))
Fixing mode	By screw panel Clip-on 35 mm symmetrical DIN rail
Marking	CE
Width	22.5 mm
Product weight	0.034 kg

Environment

Connections - terminals	Screw clamp terminals, flexible cable with cable end 1 x 0.2...1 x 2.5 mm ² / AWG 24...AWG 14 Screw clamp terminals, flexible cable with cable end 2 x 0.5...2 x 1.5 mm ² / AWG 20...AWG 16 Screw clamp terminals, solid cable without cable end 1 x 0.2...1 x 2.5 mm ² / AWG 24...AWG 14 Screw clamp terminals, solid cable without cable end 2 x 0.2...2 x 1.5 mm ² / AWG 24...AWG 16
Standards	IEC 61984
Ambient air temperature for storage	-55...85 °C
Ambient air temperature for operation	-40...55 °C
IP degree of protection	IP20 conforming to EN/IEC 60529
Dielectric strength	2500 V

Contractual warranty

Warranty period	18 months
-----------------	-----------