

# AP9631

## UPS Network Management Card 2 with Environmental Monitoring



### Overview

Model Name	UPS Network Management Card 2 with Environmental Monitoring
Includes	CD with software , Temperature Sensor , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahamas , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , Colombia , Congo , CONGO , THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , <![CDATA[Cote D'Ivoire]]> , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominica , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Grenada , Guadeloupe , Guatemala , Guinea , Guyana , French Guiana , Haiti , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Reunion , Romania , Russian Federation , Rwanda , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Turks And Caicos Islands , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe

### General

Number of Universal Sensor Ports	0
Number of Sensor Pods Supported	0
Number of Universal Sensors Supported	0
Number of Ports	0

### Communications & Management

Protocols	HTTP , HTTPS , IPv4 , IPv6 , NTP , SMTP , SNMP v1 , SNMP v2c , SNMP v3 , SSH V1 , SSH V2 , SSL , TCP/IP , Telnet
-----------	--

Network Interface Connections	RJ-45 10/100 Base-T
Authentication	Radius

## Physical

Net Weight	0.09 kg
Maximum Height	38.0 mm
Maximum Width	121.0 mm
Maximum Depth	114.0 mm
Shipping Weight	0.34 kg
Shipping Height	51.0 mm
Shipping Width	235.0 mm
Shipping Depth	159.0 mm
Color	Black
Units per Pallet	0.0

## Environmental

Operating Environment	0 - 45 °C
Storage Temperature	-5 - 45 °C
Operating Relative Humidity	0 - 95 %
Storage Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Elevation	0-15000 meters

## Conformance

Approvals	AS/NZS 3548 (C-Tick) Class A , EN 55022 Class A , EN 55024 , FCC Part 15 Class A , GOST , ICES-003 , VCCI Class A
Standard warranty	2 years repair or replace

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant
Battery Notes	Battery Notes
Other Environmental Compliance	China RoHS