



Main

Range of product	OsiSense XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Product specific application	-
Sensor name	XSD
Sensor design	Form 80 x 80 x 40
Size	40 mm
Body type	Fixed
Enclosure material	Plastic
Type of output signal	Discrete
Wiring technique	2-wire
[Sn] nominal sensing distance	60 mm
Discrete output function	1 NO
Electrical connection	Screw-clamp terminals
[Us] rated supply voltage	DC
IP degree of protection	IP67

Complementary

Detection face	Frontal
Detector flush mounting acceptance	Non flush mountable
Material	Plastic
Front material	Plastic
Output circuit type	DC
Cable entry	1 entry tapped for Pg 13.5 cable gland
Switching capacity in mA	1.5...100 mA
Switching frequency	<= 20 Hz
Marking	CE

Depth	40 mm
Height	100 mm
Width	80 mm

Environment

Product certifications	CCC
Ambient air temperature for operation	-25...70 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1136 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available End of life manual
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------