
Product datasheet Characteristics

NSYTBS11116

ABS box IP66 IK07 RAL7035 Int.H105W105D55 Ext.H116W116D62 Opaque cover H10



Main

Range	Thalassa	
Product name	Thalassa TBS	÷
Device application	Multi-purpose	
Product or component type	Industrial box	
Height	116 mm	(} :=
Width	116 mm	
Depth	62 mm	<u> </u>
Internal height	105 mm	
Internal width	105 mm	
Internal depth	55 mm	
Enclosure mounting	Wall mounted	
Device composition	1 x body	
	1 x cover	
	4 x cover screw	2
Quantity per set	Set of 5	*
Body type	One piece moulded	<u>.</u> 5
Type of front cover	Low plain cover	ţ
Cover fixing	Plastic screws	
Lock type	Outside sealed area: flat screwdriver captive screw	
Removable parts	Cover, by captive screws	0

Complementary

Material	ABS	
Colour	Grey (RAL 7035)	
Standards	IEC 62208	
Product certifications	DEMKO SEMKO TÜV	i

IP degree of protection	IP66conforming to NEMA 4.4X
IK degree of protection	IK07conforming to IEC 62262
Fire resistance	650 °C conforming to IEC 60695-2-11
Ambient air temperature for storage	-1540 °C
Ambient air temperature for operation	-2560 °C

Offer Sustainability

Sustainable offer status	Not Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity	
	Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
	Reference not containing SVHC above the threshold	
Product end of life instructions	Need no specific recycling operations	

Contractual warranty

Warranty period 18 months		
	Warranty period	18 months