



Main

Range of product	Altivar
Product or component type	Communication module



Complementary

Range compatibility	Altivar 32 Lexium 32 Altivar Easy 610 Altivar Process ATV600 Altivar Process ATV900 Altivar Machine ATV320 Altivar Machine ATV340
Communication port protocol	Profibus DP V1
Electrical connection	1 female connector SUB-D 9
Transmission rate	9.6 kbps...12 Mbps
Addressing	Configuration settings 1...126 configurable by graphic terminal/SoMove software
Communication service	4 configurable telegrams Mapping of the process data from the master Parameters management compliant with PROFIdrive V4.1 Several DP V1 messaging modes Drive profile native ATV32 conforming to IEC 61800-7-201 (CiA 402)
Display type	1 LED for RUN 1 LED for bus fault (BF)
Alarm function	Diagnostic data with VSD status Host drive handled from two masters (MS0 and MS1) Standard identification and maintenance requests
Bus profile	CiA 402 PROFIdrive
Standards	IEC 61800-7-201 (CiA 402)

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0936 - Schneider Electric declaration of conformity

 [Schneider Electric declaration of conformity](#)

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available  Product environmental
Product end of life instructions	Available  End of life manual

Contractual warranty

Warranty period	18 months
-----------------	-----------