



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	M12 plunger head
Product compatibility	XCKT XCKD XCMD XCKP
Associated body	ZCMD39L2 ZCMD37L2 ZCMD21L5 ZCMD21M12 ZCMD37L1 ZCMD41L1 ZCMD25L5 ZCMD61M12 ZCMD21L08U78 ZCMD41L2 ZCMD41L5 ZCMD29L1 ZCMD29L2 ZCMD21L08R12 ZCMD81L5 ZCMD25L1 ZCMD25L2 ZCMD21C12 ZCMD29C12 ZCMD69C12 ZCMD37L5 ZCMD39L1 ZCMD21L2 ZCMD61C12 ZCMD81L2 ZCMD21L1 ZCMD81L1 ZCMD39L5 ZCMD29L5

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Movement of operating head	Linear
Type of operator	Roller plunger spring return metal
Type of approach	Lateral approach 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------