



## Main

Product or component type	Communication card
Range compatibility	Altivar 61Q Altivar 71 Altivar 71Q Altivar 61
Communication port protocol	Modbus TCP
Product specific application	For daisy chain mounting
Connector type	1 RJ45
Transmission rate	100 Mbps 10 Mbps
Physical interface	Ethernet 2
Web services	Altivar viewer FDR Agent Security IO Scanner Altivar chart E-mail Data editor Ethernet statistics

## Complementary

Exchange mode	Half duplex and full duplex
Communication data link	MAC : IEEE 802.3 LLC : IEEE 802.2
Communication network type	IP conforming to RFC791
Communication transport type	8 connections maximum TCP conforming to RFC793 UDP
Concept	Transparent Ready class C20
Web server	Embedded
Communication service	CiA 402 profile Communication monitoring can be inhibited, adjustable

	Diagnostics (08) FTP I/O profile I/O scanning service can be inhibited Read device identification (43) Read holding registers (03) Read input registers (04) Read/Write multiple registers (23) SNMP TFTP Write multiple registers (16) Write single register (06)
Display type	1 LED for 10/100 Mbps (speed) 1 LED for FLT (Ethernet fault) 1 LED for RX (reception) 1 LED for STS (IP address) 1 LED for TX (transmission) Graphic display terminal for control word received Graphic display terminal for reference received Web server
Product weight	0.3 kg
<b>Contractual warranty</b>	
Warranty period	18 months