



Main

Range	TeSys
Device short name	LA4K
Product or component type	Suppressor module
Product compatibility	LC1 LP1

Complementary

Mounting location	Front side
Mounting mode	Clip-on
Suppressor technology	Varistor (peak limiting)
Control circuit voltage	50...129 V AC 50...129 V DC
Maximum peak voltage	2 Uc
Local signalling	LED
Quantity per set	Set of 5
Height	25 mm
Width	6 mm
Depth	22 mm
Product weight	0.01 kg

Environment

Standards	IEC 60947 BS 5424 VDE 0660 NF C 63-110
Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TC conforming to IEC 60068

TC conforming to DIN 50016

Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-50...80 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------