



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ6H7 ZCKJ2 ZCKJ7 ZCKJ7H7 ZCKJ9 ZCKJ7H29 ZCKJD37H29 ZCKJ2H7 ZCKJ1H29 ZCKJ11H29 ZCKJD39H29 ZCKJ8 ZCKJ11 ZCKJ21H7 ZCKJ5H7 ZCKJ1H7 ZCKJD31H29 ZCKJ9H29 ZCKJD35H29 ZCKJ9H7 ZCKJD31H7 ZCKJD35 ZCKJD35H7 ZCKJD39H7 ZCKJ1 ZCKJ21H29 ZCKJ5 ZCKJ8H29 ZCKJ6 ZCKJD37 ZCKJD37H7 ZCKJ8H7 ZCKJ11H7

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKJD31
ZCKJ6H29
ZCKJ5H29
ZCKJ2H29
ZCKJD39
ZCKJ21

Movement of operating head	Linear
Type of operator	Side plunger spring return metal
Type of approach	Lateral approach 1 direction

Complementary

Switch actuation	On end
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0951 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------