

ZCKE65
limit switch head ZCKE - metal side plunger with
vertical roller



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJD35H7 ZCKJD31H7 ZCKJ9H7 ZCKJ7H7 ZCKJD35 ZCKJ8H29 ZCKJ6H7 ZCKJ8H7 ZCKJ1H29 ZCKJ5H29 ZCKJ8 ZCKJ9 ZCKJ21H7 ZCKJ5H7 ZCKJ7H29 ZCKJD37H7 ZCKJ6 ZCKJ7 ZCKJ2H7 ZCKJD35H29 ZCKJD31 ZCKJ1H7 ZCKJ11 ZCKJ1 ZCKJD39 ZCKJ11H7 ZCKJ9H29 ZCKJ21H29 ZCKJD37 ZCKJD31H29 ZCKJ2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKJ21
 ZCKJD39H29
 ZCKJD37H29
 ZCKJ6H29
 ZCKJD39H7
 ZCKJ5
 ZCKJ11H29
 ZCKJ2H29

Movement of operating head	Linear
Type of operator	Side roller plunger spring return metal (with vertical roller)
Type of approach	Vertical approach 2 directions


Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0951 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------