



### Purchase

APC  
 P6B

### Overview

Model Name	APC Essential SurgeArrest, 6 outlet
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Aruba , Barbados , Bermuda , Bahamas , Belize , Canada , Guyana , Haiti , Jamaica , Cayman Islands , Turks And Caicos Islands , Trinidad And Tobago , United States , VIRGIN ISLANDS (UNITED STATES)

### Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	1.83 meters

### Surge Protection and Filtering

Surge energy rating	840 joules
---------------------	------------

### Physical

Maximum Height	292 mm
Maximum Width	57 mm
Maximum Depth	38 mm
Net Weight	0.45 kg
Shipping Weight	0.6 kg
Shipping Height	338 mm
Shipping Width	147 mm
Shipping Depth	38 mm
Master Carton Units	12.0

Master Carton Dimensions (Length x Width x Height)	16 inches
Master Carton Weight	18.52 lbs
Color	Charcoal
SCC Codes	1073130421102 7
Units per Pallet	288.0

### Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

### Conformance

Approvals	CSA , UL 1449
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$25000