

UL PC 175/85 XHG

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws



Sample Photo

Product #: 6013339
 Description: PC Enclosure
 Remarks: Extra High base, grey cover
 Package: 1
 Unit: PCS
 Product group: MNX PC Enclosures

EAN: 6418074011695
 ETIM: EC000261 EC000261

Dimensions:	
Length (mm):	180.0
Width (mm):	180.0
Height (mm):	85.0
Length (inch):	7.1
Width (inch):	7.1
Height (inch):	3.3

Support items:

- [Product card \(PDF\)](#)
- [Dimensional drawing \(mm\)](#)
- [Dimensional drawing \(inch\)](#)
- [Cad-files \(registration needed\)](#)

Ratings:	
Ingress Protection (EN 60529):	IP66/67
Impact Resistance (EN 62262):	IK08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C:	960
NEMA Class:	NEMA 4, 4X, 6

Materials:		Temperatures:	
Material:	Polycarbonate	Temperature °C (short term):	-40 ... 140 °C
Base colour:	RAL 7035 -light grey	Temperature °C (continuous):	-40 ... 80 °C
Cover screws material:	Polyamide	Temperature °F (short term):	-40 ... 284 °F
Cover colour:	RAL 7035 -light grey	Temperature °F (continuous):	-40 ... 175 °F
Gasket material:	TPE		

Data subject to change without notice