

## UL PCM 125/75 G



Sample Photo

**Including:** Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Product #: 6016308  
Description: Enclosure, PC, metric knock-outs  
Remarks: Grey cover  
Package: 60  
Unit: PCS  
Product group: MNX PCM Enclosures

EAN: 6418074038043  
ETIM: EC000261 EC000261

| Dimensions:    |       |
|----------------|-------|
| Length (mm):   | 130.0 |
| Width (mm):    | 130.0 |
| Height (mm):   | 75.0  |
| Length (inch): | 5.1   |
| Width (inch):  | 5.1   |
| Height (inch): | 3.0   |

### Support items:

[Product card \(PDF\)](#)  
[Dimensional drawing \(mm\)](#)  
[Dimensional drawing \(inch\)](#)  
[Cad-files \(registration needed\)](#)

| Ratings:                               |                   |
|----------------------------------------|-------------------|
| Ingress Protection (EN 60529):         | IP66/67           |
| Impact Resistance (EN 62262):          | IK08              |
| Electrical insulation:                 | Totally insulated |
| Halogen free (DIN/VDE 0472, Part 815): | 1                 |
| UV resistance:                         | UL 508            |
| Flammability Rating:                   | UL 746C 5"        |
| Glow Wire Test (IEC 695-2-1) °C:       | 960               |
| NEMA Class:                            | NEMA 4, 4X, 6     |

| Materials:             |                      | Temperatures:                |                |
|------------------------|----------------------|------------------------------|----------------|
| Material:              | Polycarbonate        | Temperature °C (short term): | -40 ... 140 °C |
| Base colour:           | RAL 7035 -light grey | Temperature °C (continuous): | -40 ... 80 °C  |
| Cover screws material: | Polyamide            | Temperature °F (short term): | -40 ... 284 °F |
| Cover colour:          | RAL 7035 -light grey | Temperature °F (continuous): | -40 ... 175 °F |
| Gasket material:       | TPE                  |                              |                |

Data subject to change without notice

**FIBOX**  
Enclosing innovations