

General Information

Extended Product Type:	DR2.5/10.P.4L
Product ID:	1SNA290219R1200
EAN:	3472592902197
Catalog Description:	DR2.5/10.P.4L Spring Terminal Blocks - Miniblocks - Green-Yellow
Long Description:	- Save space with compact angled terminal blocks, - Easy mounting on DIN rail TH15, - Easy to access thanks to the front wiring entry, - Clamping contact pressure non dependent on the operator and automatic creeping compensation.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
Color:	Green-Yellow
Connecting Capacity Main Circuit UL/CSA:	Spring Clamp / Flexible 1x 26 ... 12 AWG
Connecting Capacity UL/CSA:	Stranded 12 AWG
Connecting Capacity Main Circuit:	Spring Clamp / Flexible 1x 0.12 ... 2.5 mm ² Spring Clamp / Rigid 1x 0.12 ... 4 mm ² Spring Clamp / With Insulated Ferrule 1x 0.5 ... 1.5 mm ²
Connection Type:	Spring
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC160020C0201
Declaration of Conformity - CE:	1SND225021U1000
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
EAC Certificate:	1SND162001A1100
EAN:	3472592902197
ETIM 4:	EC000901 - Ground terminal block
ETIM 5:	EC000901 - Ground terminal block
ETIM 6:	EC000901 - Ground terminal block
Environmental Information:	1SND220032E1002
Flammability According to UL94:	V0
Function:	Miniblock
Gauge Type:	A2
Gauge(s) of Form:	A2
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160020C0201
Insulation Material:	Polyamide
Invoice Description:	DR2.5/10.P.4L Spring Terminal Blocks - Miniblocks - Green-Yellow
Minimum Order Quantity:	100 piece
Mounting on DIN Rail:	TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715
Number of Connections:	4
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	100 piece

Package Level 1 EAN:	3472592902197
Package Level 1 Gross Weight:	0.7 kg
Package Level 1 Height:	75 mm
Package Level 1 Length:	200 mm
Package Level 1 Units:	100 piece
Package Level 1 Width:	176 mm
Package Level 2 Gross Weight:	6.8 kg
Package Level 2 Height:	300 mm
Package Level 2 Length:	500 mm
Package Level 2 Units:	900 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	21600 piece
Pollution Degree:	3
Product Main Type:	DR2.5/10.P.4L
Product Name:	Terminal block
Product Net Depth:	24.5 mm
Product Net Height:	33 mm
Product Net Weight:	7 g
Product Net Width:	10 mm
Product Packing Type:	Box
RMRS Certificate:	1SND162000A1101
Rated Cross-Section:	2.5 mm ²
Rated Short-time Withstand Current (I _{cw}):	for 1 s 300 A
Recommended Screw Driver:	3.5 mm
RoHS Date:	Z
RoHS Information:	1SND230488F0201
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	Spring Terminal Blocks DR2.5/10.P.4L-GN--YL
Spacing:	10 mm
Sub-Function:	Ground
Sub-Function 3:	Rail mounting TH15-5.5
Sub-Function 4:	Ground with 4 connections
Wire Stripping Length:	9.5 mm
Number of Potentials:	1

