MALLORY Mallor	y Sonale	rt Products	Part #: JT028-RY-CD			
Sales Outline Drawing				Revision:	В	
Specifications:						
Stack Number:	1	2				
LED Color:	RED	YELLOW		<u> </u>		
Connection Wires:	Red and Brown	Yellow and Brown				
LED Current Draw:	<50mA	<60mA				
Rated Voltage:	24 VAC/DC					
Operating Voltage:	20-28 VAC/DC					
Total Max Current:	<110mA					
Operating Temperature:	-25° ~ +60°C					
Lens Color:	Opaque White					
Material:	ABS FR15U					
Mounting Method:	Direct Mount using 1/2" NPT Stainless Steel Pipe and Nut					
Weight Typical (g):	210					
NEMA 12:	Approved					
Options:	Please contact factory.					
Dimensions: Inches	•	cUL Recognized			ROHS Compliant	
		YELLOW [114.3] 2.4 [61.8]	0.88 [Ø22.2] Knock dut - For Wires	8" re		
	'	TOP VIEW MOUNTING DIAGRAM				
LED OPERATION: CONN	IECT STACK COL	OR WIRE TO POWER A	ND BROWN WIR	E TO POWER.		