
Part #: **Mallory Sonalert Products, Inc.** JT028-YG-CDL Revision: **Sales Outline Drawing** В **Specifications:** Stack Number: LED Color: YELLOW **GREEN Connection Wires:** Yellow and Brown Green and Brown LED Current Draw: <60 mA <40 mA Rated Voltage: 24 VAC/DC Operating Voltage: 20-28 VAC/DC Sound Level Category: Loud Loud Loud Loud Continuous for 5 sec then 0.1s Mode of Operation: Continuous Medium Pulse (5PPS) Double Pulse (0.5PPS) beep until reset Black and Gray Wires; Black and Gray Wires; Black and Gray wires; Orange and Black and Gray Connection: Orange wire connected Purple wire connected to Purple wires connected to Wires to Green/Yellow wire Green/Yellow wire Green/Yellow wire 40mA Max. 40mA Max. 40mA Max. 40mA Max. Sound Current Draw: 80-85 dB(A) Typ. Loudness @ 1m: Frequency: 2000 ± 500 Hz Total Max Current: <140mA with all LED's and Sound unit working Operating Temperature: -25° ~ +60°C Lens Color: Opaque White Material: ABS FR15U Direct Mount using 1/2" NPT Stainless Steel Pipe and Nut Mounting Method: Weight Typical (g): 315 NEMA 12: Approved Options: Please contact factory.

Dimensions: Inches (mm)

cUL Recognized

ROHS Compliant



LED OPERATION: CONNECT STACK COLOR WIRE TO POWER AND BROWN WIRE TO POWER.

SOUND OPERATION: CONNECT GRAY AND BLACK WIRES TO POWER FOR CONTINUOUS SOUND.

FOR MEDIUM PULSE, CONNECT GRAY & BLACK TO POWER AND ORANGE WIRE TO GREEN/YELLOW

FOR DOUBLE PULSE, CONNECT GRAY & BLACK TO POWER AND PURPLE WIRE TO GREEN/YELLOW

WIRE.
FOR CONT/BEEP, CONNECT GRAY & BLACK TO POWER AND ORANGE & PURPLE TO

GREEN/YELLOW WIRE.