



The WAGO Communication Cable provides a simple option for communication with WAGO software tools (WAGO-I/O-CHECK, WAGO-I/O-PRO, ...).

Notice: The communication cable shall not be connected or removed when energized.

The WAGO USB Communication Cable connects a PC (notebook) to either the service interface of the 857 Series Signal Conditioners and Relay Modules (JUMPFLEX), or to WAGO-I/O-SYSTEM buscouplers/controllers.

Notice:
Using the WAGO 759-923 USB Communication Cable in combination with select programmable fieldbus controllers requires the specific firmware versions

Description	Item No.	Pack. Unit
Communication cable (used to register or remove the end extension module)	750-920	10
Technical Data		
Ports	4-pole service connectors	
Length	2.5 m	
Operating temperature	0 °C ... +55 °C	
Degree of protection	IP20	
Weight	77.9 g	
Connector dimensions (WxHxD)	15 x 50 x 19 mm	

Description	Item No.	Pack. Unit
WAGO USB Communication Cable, length 2.5 m	750-923	1
WAGO USB Communication Cable, length 5 m	750-923/000-001	1
Technical Data		
USB specification	2.0 compatible/full-speed device	
Operating system	Microsoft® Windows® 2000; Microsoft® Windows® XP Professional; Microsoft® Windows® Vista®; Microsoft® Windows® 7	
Operating temperature	-25 °C ... +70 °C	
Interface USB	Type A/m	
Length	2.5 m (750-923)	
	5 m (750-923/000-001)	
Connector dimensions (WxHxD)	15 x 50 x 19	
Test voltage	2.5 kV, 50 Hz, 1 min.	
EMC immunity of interference	acc. to EN 61000-4-3, EN 61000-4-6	
EMC emission of interference	acc. to EN 55022	
Approvals		
Conformity marking	CE	