

8-Port 1U Rack-Mount USB/PS2 KVM Switch with On-Screen Display

MODEL NUMBER: **B042-008**



Description

Tripp Lite's NetController 8-Port, 1U rackmount KVM Switch is an affordable, highly-flexible enterprise class KVM Switch, which allows the user to connect either USB or PS/2 keyboards and mice. In addition, P780-Series USB/PS2 combo KVM cable kits allow you to connect either USB or PS/2 computers, without the need to purchase separate cables or adapters. Control up to 8 directly connected computers, or expand the number of connected computers to up to 248 by daisy chaining up to 15 additional B042-Series KVM switches. Switch between connected computers via the On-Screen Display (OSD), pushbuttons, or keyboard hotkey commands. Other features include: password protection, auto-scanning, auto-logout, firmware upgrade and video support up to 2048 x 1536 (QXGA). Mounts easily in a standard 19" rack/cabinet and includes all necessary mounting hardware. Compatible with all major operating systems. Constructed of heavy-duty steel housing.

Features

- NetController 8-Port, 1U rackmount KVM switch
- Control 8 computers via a single VGA monitor and USB or PS/2 keyboard/mouse
- P780-Series USB/PS2 combo KVM cable kits allow you to connect either USB or PS/2 computers, without the need to purchase separate cables or adapters
- Control up to 248 computers by daisy chaining up to 15 additional B042-Series KVM switches
- Allows for easy customization of ports by daisy-chaining any combination of B042-Series KVM's (4-, 8- or 16-port)
- Standard 19" Rackmount size - hardware included
- On-Screen Display (OSD) menu for intuitive operation and easy control
- Switch between connected computers via the On-Screen Display (OSD), pushbuttons, or keyboard hotkey commands
- Supports video resolution up to 2048 x 1536
- Password protection and auto-logout features
- Firmware upgradeable
- Robust metal case design ensures best EMI/RFI shielding and video quality

Highlights

- NetController 8-Port, 1U rackmount KVM switch
- Control 8 computers via a single VGA monitor and USB or PS/2 keyboard/mouse
- Control up to 248 computers by daisy chaining up to 15 additional B042-Series KVM switches
- P780-Series USB/PS2 combo KVM cables kits allow you to connect either USB or PS/2 computers, without the need to purchase separate cables or adapters
- Compatible with all major operating systems

Package Includes

- B042-008 NetController 8-Port, 1U rackmount KVM switch
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A / Output: 9V, 1A)
- Rackmount hardware
- 8 In. Daisychain cable (for longer daisy-chain cables, see Tripp Lite P781 series cables)
- Daisychain terminator
- 4 ft. HD15 to DB9 firmware upgrade cable
- CD with owner's manual and quick start guide
- Quick start guide



- Hot-swappable: disconnect and reconnect USB computers without rebooting
- Supports standard 5-button Microsoft, Logitech, or comparable mice
- Supports standard Microsoft, Logitech, or comparable keyboards
- Compatible with all major operating systems
- Constructed of heavy-duty steel housing

Specifications

OVERVIEW	
Users	1
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A / Output: 9V, 1A
Console	No
Max CPU	248
PHYSICAL	
Color	Black
LCD Monitor (in.)	Not Applicable
LCD Monitor (cm)	Not Applicable
ENVIRONMENTAL	
BTUs	245.52
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys, OSD
IP Remote Access	No
CONNECTIONS	
Ports	8
PC/Server Connections	VGA; USB; PS/2
SPECIAL FEATURES	
Cat5 KVM Switch	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>