

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Universal Reversible USB 2.0 Hi-Speed Extension Cable (Reversible A to A M/F), 1-ft.

MODEL NUMBER: UR024-001



Description

This 1-ft USB extension cable features a Universal / Reversible, A-Male connector, and is manufactured using USB2.0 cable. Universal / Reversible connector allows the cable to be plugged in any direction. This cable is backwards compatible and can also be used with the older USB 1.1 cables. Made with superior foil shielding for reliable error-free data communications. Features nickel plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) makes it perfect for multimedia applications.

Features

- 1ft, USB 2.0 A-Male to A-Female Extension, with Universal / Reversible "A" Male connector
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- · Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair, 24AWG Power pair

Specifications

INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.3
PHYSICAL	
Color	Black

Highlights

- Universal / Reversible A-Male
 plugs in any direction
- Extend distances of USB 2.0 cables with this extension cable
- Supports faster data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices, especially multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28/24 AWG data lines
- Gold plated contacts provide superior conductivity

System Requirements

- Any USB device requiring a USB cable
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

Universal Reversible USB 2.0
 A-Male to A-Female Extension
 Cable - 1ft



ENVIRONMENTAL		
Operating Temperature Range	-10/+75° C (14 to 167° F)	
Storage Temperature Range	-20/+80° C (-4 to 176° F)	
CONNECTIONS		
Side A - Connector 1	REVERSIBLE USB A (MALE)	
Side B - Connector 1	USB A (FEMALE)	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies