

Heavy-Duty Power Extension Cord, 15A, 14AWG (IEC-320-C14 to IEC-320-C13), 18-in.

MODEL NUMBER: P005-18N



Highlights

- C13 to C14 Power Cable, 1.5-ft.
 (18 in.)
- 14 AWG x 3C
- 15A / 100 250V
- RoHS Compliant
- UL Listed

Package Includes

C13 to C14 Power Cable, 1.5-ft.
 (18 in.)

Description

Use Tripp Lite's P005-18N in server applications that require a high-rated, heavy-gauge cable. Its short length is perfect for server to PDU or UPS connections that are in close proximity. C13 to C14 connectors, 3 x 14 AWG conductors, 15A rating and 100-250V.

Features

- Short length reduces rack cable clutter
- Molded, heavy-duty power cable, 1.5-ft. (18 in.)
- IEC-320-C13 to IEC-320-C14
- 14 AWG x 3C, SJT, 15A, 100-250 Volt
- RoHS Compliant
- UL Listed

Specifications

INDUT					
INPUT					
Cable Length (ft.)	1.5				
Cable Length (m)	0.5				
Cable Length (in.)	18				
Cable Length (cm)	45.72				
PHYSICAL					
Color	Black				
	·				
ENVIRONMENTAL					



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Operating Temperature Range	-4 F (-20 C) to 140 F (60 C)
Storage Temperature Range	-4 F (-20 C) to 140 F (60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies