

USB 2.0 Hi-Speed Panel Mount Extension Cable (A/A M/F), 6-in.

MODEL NUMBER: U024-06N-PM



Description

This 6-in. Panel Mount USB extension cable is manufactured using USB2.0 cable. It features a panel mount connector that allows you to secure a USB A female port in a fixed location, such as a motherboard, podium, or kiosk. It is designed for use with USB 2.0 device cables, but is backwards compatible and can also be used with

Highlights

- Secure a USB A female port in a fixed location, such as a motherboard, podium, or kiosk
- Extend distances of USB 2.0 cables with this extension cable
- Data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28/20 AWG data lines

System Requirements

 Any device requiring a longer USB cable

Package Includes

 U024-06N-PM 6 in. Panel Mount USB 2.0 Extension Cable (USB A M/F)

USB 1.1 cables. Made with superior foil shielding for reliable error-free data communications. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- Secure a USB A female port in a fixed location, such as a motherboard, podium, or kiosk
- Extend distances of USB 2.0 cables with this extension cable
- Data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil feature twisted 28/20 AWG data lines

Specifications

| INPUT | | |
|----------------------|--------------|--|
| Cable Length (ft.) | 0.5 | |
| Cable Length (m) | 0.2 | |
| PHYSICAL | | |
| Color | Black | |
| CONNECTIONS | | |
| Side A - Connector 1 | USB A (MALE) | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| Side B - Connector 1 | USB A (FEMALE) - PANEL MOUNT |
|-------------------------------------|------------------------------|
| CERTIFICATIONS | |
| CENTI IOATIONS | |
| Certifications | RoHS compliant |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies