

External 24V 3U Rack/Tower Battery Pack for select Tripp Lite UPS Systems (BP24V70-3U)

MODEL NUMBER: BP24V70-3U



Highlights

- Extends the runtime of expandable 24V DC Tripp Lite UPS Systems
- Included daisychain connector supports the addition of multiple compatible external battery packs
- Supports 3U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount and tower installation available

Package Includes

- BP24V70-3U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual

Description

BP24V70-3U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 24V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included daisychain connector enables the connection of additional compatible 24V external battery packs to the host UPS. Included mounting accessories support 3U rackmount installation in 4 post racks. Options for 2 post center-mounting and upright tower installation available.

Compatible with these UPS Systems - [OMNIVS1500XL](#), [OMNIVSINT1500XL](#), [SMART750RML2U](#), [SMART750XLA](#), [SU750RTL2U](#), [SU750RTLCD2U](#), [SU750XL](#), [SU1000RTL2UA](#), [SU1000RTLCD2U](#), [SU1000XLA](#), [SU1000XLCD](#), [SUINT1000RTL2UA](#) and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 24V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Daisychain connector enables the connection of additional compatible 24V external battery packs to the host UPS
- Included mounting brackets support rackmount installation in 4 post racks using only 3 rack spaces (3U)
- [2POSTRMKITHD](#) option supports balanced 2 point center-mounting in 2 post equipment racks
- [2-9USTAND](#) option enables upright tower placement

Specifications

BATTERY	
DC System Voltage (VDC)	24
UPS Connection	Attached cable with red/black 75 amp male DC connector
Typical Battery Lifespan	4-6 years typical (North America)



PHYSICAL	
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount(2POSTRMKITHD); Tower(2-9USTAND)
Minimum Required Rack Depth (inches)	28
Minimum Required Rack Depth (cm)	71.12
Shipping Dimensions (hwd / in.)	11.5 x 23 x 33
Shipping Dimensions (hwd / cm)	29.2 x 58.4 x 83.8
Shipping Weight (lbs.)	176.37
Shipping Weight (kg)	80.07
Unit Dimensions (hwd / in.)	5.25 x 17.5 x 25
Unit Dimensions (hwd / cm)	13.33 x 44.45 x 63.5
Unit Weight (lbs.)	138.89
Unit Weight (kg)	63.00
Material of Construction	Steel
External Battery Pack Form Factor	Rack/Tower
Minimum Required Rack Depth (mm)	711
WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>