

SmartRack 18U Heavy-Duty Low-Profile Server-Depth Side-Mount Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: **SRW18UHD**



Description

The SRW18UHD SmartRack 18U Heavy-Duty Low-Profile Server-Depth Side-Mount Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 500 pounds.

Because the low-profile cabinet mounts sideways, it extends less than 25 inches from the wall while housing equipment up to 32.5 inches deep, including 1U servers, UPS systems, battery packs, network switches and patch panels.

The removable front panel and side doors lock securely to help prevent damage, tampering or theft. The top, bottom and sides are vented, which allows air to flow freely and keep equipment cool. Convenient top and bottom ports allow easy cable routing.

The SRW18UHD comes fully assembled and ready to mount to the wall. Square and 12-24 threaded mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails adjust in 7/8-inch increments.

Features

Saves Valuable Workspace

- Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way
- Houses EIA-standard 19 in. rack equipment in 18U of space
- Extends less than 25 in. from the wall while housing 1U servers, UPS systems, battery packs, network switches and patch panels up to 32.5 in. deep
- Maximum load capacity of 500 lb.

Keeps Important Equipment Secure

- Sides and front lock securely to help prevent damage, tampering or theft

Highlights

- Maximum load capacity of 500 lb.
- Locking steel cabinet vented at sides, top and bottom
- Flow-through ventilation keeps equipment cool
- Secures 18U of 19 in. rack equipment up to 32.5 in. deep

Package Includes

- SRW18UHD SmartRack 18U Heavy-Duty Low-Profile Server-Depth Side-Mount Wall-Mount Rack Enclosure Cabinet
- (42) M6 screws
- (42) M6 cage nuts
- (42) M6 washers
- (42) 12-24 screws
- (2) Keys
- Owner's manual



- Vented panels allow generous airflow that keeps equipment cool
- Convenient ports with removable covers allow cable routing through top and bottom

Easy Enclosure and Equipment Installation

- Ships fully assembled for quick installation
- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Vertical mounting rails adjust in 7/8 in. increments
- Rails support square-hole or 12-24 threaded-hole mounting
- Rack spaces numbered for easy reference

Meets Payment Card Industry Standards

- Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

PHYSICAL	
Rack Height (U Spaces)	18
Maximum Device Depth (in.)	32.5
Maximum Device Depth (cm)	82.55
Minimum Device Depth (in.)	3
Minimum Device Depth (cm)	7.62
Shipping Dimensions (hwd / in.)	41.33 x 37.8 x 25.6
Shipping Dimensions (hwd / cm)	104.9 x 96 x 65
Shipping Weight (lbs.)	137.5
Shipping Weight (kg)	62.36
Unit Dimensions (hwd / in.)	36.96 x 36.22 x 24.77
Unit Dimensions (hwd / cm)	93.88 x 92 x 62.92
Unit Weight (lbs.)	119.9
Unit Weight (kg)	54.39
Color	Black
Weight Capacity - Stationary (lbs.)	500
EIA Mounting Rails	Square holes / 12-24 threaded holes
Weight Capacity - Stationary (kg)	227
Maximum Device Depth (mm)	826
Minimum Device Depth (mm)	76
CERTIFICATIONS	
Certifications	EIA-310-E



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>