

# Ledex® Low Profile Size 5SF — Push or Pull

Short Stroke, Flat Face  
Part Number: 129450-0XX

All catalog products manufactured after  
April 1, 2006 are RoHS Compliant

## Performance

Maximum Duty Cycle	100%	50%	25%	10%
Maximum ON Time (sec) when pulsed continuously <sup>1</sup>	∞	100	36	10
Maximum ON Time (sec) for single pulse <sup>2</sup>	∞	160	44	13
Watts (@ 20°C)	21	42	84	210
Ampere Turns (@ 20°C)	860	1220	1720	2730

### Coil Data

awg (0XX) <sup>3</sup>	Resistance (@20°C)	# Turns <sup>4</sup>	VDC (Nom)	VDC (Nom)	VDC (Nom)	VDC (Nom)
23	2.03	288	6.1	8.6	12.1	19.2
24	3.20	360	7.6	10.8	15.3	24.0
25	4.91	440	9.6	13.6	19.2	31.0
26	7.72	550	12.1	17.1	24.0	38.0
27	11.12	636	15.0	21.0	30.0	48.0
28	18.79	840	19.2	27.0	39.0	61.0
29	30.48	1088	24.0	34.0	48.0	77.0
30	44.86	1275	30.0	43.0	61.0	96.0
31	70.90	1596	38.0	54.0	76.0	121.0
32	109.00	1974	47.0	67.0	95.0	150.0
33	175.00	2496	60.0	86.0	121.0	192.0

- <sup>1</sup> Continuously pulsed at stated watts and duty cycle
- <sup>2</sup> Single pulse at stated watts (with coil at ambient room temperature 20°C)
- <sup>3</sup> Other coil awg sizes available — please consult factory
- <sup>4</sup> Reference number of turns

## Specifications

Dielectric Strength	23 awg, 1000 VRMS ; 24-33 awg, 1200 VRMS
Recommended Minimum Heat Sink	Maximum watts dissipated by solenoid are based on an unrestricted flow of air at 20°C, with solenoid mounted on the equivalent of an aluminum plate measuring 7½" square by ⅛" thick
Coil Resistance	23-33 awg, ±5%
Weight	9.0 oz (255 gms)
Holding Force	58.0 lb (258.0 N) @ 105°C
Dimensions	Ø1.875" x 0.880" L (See page G17)


## How to Order

Add the coil awg number (0XX) to the part number (for example: to order a 25% duty cycle unit rated at 30 VDC, specify 129450-027).

Please see [www.ledex.com](http://www.ledex.com) (click on Stock Products tab) for our list of stock products available through our North American distributors.


LINEAR Low Profile

Size 5SF— Typical Force @ 20°C



Force values for reference only.

Size 5SF— Typical Speed @ No Load, 20°C




All specifications subject to change without notice.

# Ledex® Low Profile Dimensions


Inches (mm)

All solenoids are illustrated in energized state


## Size 4EF/4EC



## Size 5SF



## Size 5EC



LINEAR Low Profile

All specifications subject to change without notice.