



Manual Tensioning Tool with Metal Housing

MK3SP up to 4.8 mm strap width

This tough metal tool MK3SP is used by harness makers for the automotive and white goods industries, as well as in aerospace, railway and medical.

Features and Benefits

- Tough metal tool for HellermannTyton plastic cable ties up to 4.8 mm width
- For consistent tensioning and automatically flush cutting
- Infinitely adjustable tensioning force
- Reliable and low maintenance



MK3SP.

TYPE	Strap Width max.	Strap Thickness max.	Weight	Article-No.
MK3SP	4.8	1.5	0.33 kg	110-03500
SP MK3SP replacement blade	-	-	0.01 kg	110-03524

All dimensions in mm. Subject to technical changes.

Pneumatic Tensioning Tool with Metal Housing

MK3PNSP2 up to 4.8 mm strap width

Features and Benefits

- Pneumatic tensioning tool
- Tough metal housing
- For cable ties up to 4.8 mm width
- For consistent tensioning and automatically flush cutting
- Infinitely adjustable tension force
- High application speed
- Reliable and low maintenance



MK3PNSP2.

Air Supply	Non oiled / oiled
Air Pressure (min.)	3 Bar
Air Pressure (max.)	6 Bar
Hose Internal Diameter	4.0 mm
L x H x W	approx. 225 x 140 x 40 mm
Specifications	CE, GS

RoHS

TYPE	Strap Width max.	Strap Thickness max.	Weight	Article-No.
MK3PNSP2	4.8	1.5	0.56 kg	110-03400
SP compressed air hose	-	-	0.35 kg	110-30002
SP MK3PNSP2 cutting blade	-	-	0.01 kg	110-30101

All dimensions in mm. Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.