

## Product data sheet

### Characteristics

# NSYMM66WH

Mounting plate - enclosure H600xW600mm - polyester powder over galvanised sheet



### Main

|                                    |  |
|------------------------------------|--|
| Range                              | Spacial                                  |
| Accessory / separate part category | Mounting accessory                       |
| Product or component type          | Mounting plate                           |
| Device application                 | Multi-purpose                            |
| Enclosure nominal dimensions       | H: -                                     |
| Mounting location                  | Step slide<br>Direct fixing on backstuds |
| Mounting plate description         | Plain                                    |
| Range compatibility                | Spacial S3DC<br>Spacial S3DCD            |
| Application market                 | Only US market                           |
| Quantity per set                   | Set of 1                                 |
| Material                           | Galvanised steel                         |
| Colour                             | White                                    |
| Surface finish                     | Epoxy-polyester powder                   |

### Complementary

|                            |   |
|----------------------------|---|
| Fixing mode                | Screwed on backstuds - screw type M8<br>By fixing element |
| Permanent permissible load | 135 kg  |
| Height                     | 550 mm  |
| Width                      | 550 mm  |
| Depth                      | 125 mm  |
| Thickness                  | 1.8 mm  |
| Product weight             | 44 kg   |

### Offer Sustainability

|                          |                           |
|--------------------------|---------------------------|
| Sustainable offer status | Not Green Premium product |
|--------------------------|---------------------------|

Contractual warranty

---

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---