



PORTABLE GFCI RIGHT ANGLE PLUG, MANUAL

1594CMM | [Pass & Seymour](#)

FEATURES & BENEFITS

Portable Ground Fault Circuit Interrupter, Right Angle Plug, 15amp 125volt, Manual Reset



- Durable polycarbonate case withstands hard use.
- Open neutral protection.
- Has bright, green power indicator light that is on when power is available.
- 10kA short circuit rating.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Yellow
Type: Portable

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Standard: C22.2 No. 144
CUL Listing No: E42190
cULus: Yes
cUL Standard: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121614

DIMENSIONS

Height (US): 4.00"
Length (US): 4.00"

Width (US): 2.00"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15P

NEMA Rating: Yes

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No