

CARDMASTER ABS 21/18-3



Order symbol: ABS 21/18-3
Product nbr: 7585154
Description: Enclosure, ABS
Remarks: Smoked transparent hinged cover

EAN: 6418074056788
EI. number:
 Finland: 3438243
 Electric No. 8212016761
 Denmark:
 Electric No. Sweden: 7585154

Including: Base, terminal compartment cover with PUR gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	235	185	119	FP 21/18 Front plate (aluminium)
inch:	9.3	7.3	4.7	FC PC 21/18 Frame of PC front plate
Materials:	Rating:			
Material: ABS	Ingress Protection (EN 60529): IP65			
Base colour: RAL 7035 -light grey	Impact Resistance (EN 62262): IK07			
Cover colour: Smoked grey	Electrical insulation: Totally insulated			
Gasket material: EPDM & PUR	Halogen free (DIN/VDE 0472, Part 815): 1			
Temperatures:				Flammability Rating: UL 94 HB
Temperature °C (short term): -40 ... 80 °C	Glow Wire Test (IEC 695-2-1) °C: 650			
Temperature °C (continuous): -40 ... 60 °C	NEMA Class: NEMA 1, 3, 3R, 12, 13			
Temperature °F (short term): -40 ... 175 °F	Certificates:			
Temperature °F (continuous): -40 ... 140 °F	Gost R			
Accessories:	MP 21/18 Mounting plate			

