



Sample photo

Order symbol: PC 200/100 HT
Product nbr: 6011927
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074022486
El. number:
Finland: 3420483
Electric No. Denmark: 8212022535
Electric No. Italy: 7352125
Electric No. Sweden: 2535672

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height
mm:	255	180	100
inch:	10.0	7.1	3.9

Materials:

Material: Polycarbonate
Base colour: RAL 7035 -light grey
Cover screws material: Polyamide
Cover colour: Smoked grey
Cover screws colour: Black
Gasket material: TPE

Temperatures:

Temperature °C (short term): -40 ... 120 °C
Temperature °C (continuous): -40 ... 80 °C
Temperature °F (short term): -40 ... 250 °F
Temperature °F (continuous): -40 ... 175 °F

Accessories:

MIV 200 Mounting plate (Galvanized steel)

Accessories:

MIN 15 DIN-15 Mounting rail
MIN 20 DIN-15 Mounting rail
MIV 15 DIN-35 Mounting rail
MIV 20 DIN-35 Mounting rail
FP A 200/180 Front plate (Aluminium)
HFP 180 Front plate hinge series
FP 22046 Wall fastening lug (4 pcs)

Rating:

Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Certificates:

Germanischer Lloyd (GL)
SGS Fimko
Gost R

